




SEPOR, INC.  
718 N. FRIES AVE.  
P. O. BOX 578  
WILMINGTON, 90748  
PHONE: 310-830-6601  
FAX: 310-830-9336



Mini-Pulverizer, End Closed



Pulverizer Plates



Mini-Pulverizer, Opened for cleaning

## Sepor Mini-Pulverizer (PGE)

The Sepor Mini-Pulverizer comes with ceramic or tungsten carbide grinding plates and is ideally suited for reducing small quantities of minus 1/4 inch material to minus 150 mesh. It has a nominal capacity for reducing 1 to 20 gram size batch samples (Quartz Ore). Plate life for ceramic plates is typically 1,000 to 3,000 individual samples of 10 grams of quartz ore reduced to 150 mesh. By reversing the direction of the plate rotation, the plate life may be maximized. A switch is provided on the crusher for reversing the plate direction. Grinding size is adjustable from 40 mesh to 150 mesh.

The pulverizer is easily cleaned with a brush, air hose or vacuum. Brushing will recover nearly all of the sample.

### FEATURES:

- Portable, countertop model
- Easy to clean
- Direction of rotation reversing switch extends plate life

**Motor:** 1/3 HP capacitor start

**Closure:** Cam action

**Shipping Weight:** 40 lbs.

**Bearings:** Sealed

**Grind Adjust:** Variable

010F-030

010F-031

010F-032

010F-033

Mini-Pulverizer with Alumina Plates

Mini-Pulverizer with Tungsten Carbide Plates

Extra Set of Alumina Plates

Extra Set of Tungsten Carbide Plates